AUTHORIZED KODAK & ST IMAGING Products
Formerly Bell & Howell

## Investment Proposal Created Especially for Bill Moehnke- Humboldt County Library

November 6, 2018

### ST ViewScan 4 – Premium 9MP Image Sensor

ST ViewScan 4 Complete System Scanner Base / Universal Carrier 9 Megapixel Image Camera Sensor 7x-105x Magnification, 3.0 USB	1 UNIT \$5,195.00
Perfect View Standard Software Includes: Browse, crop, save to disk, CD, thumb drive, and print	Incl.
ST Micro PC- Mounted on Scanner Intel Core i5, 2.5GHz, 8GB, W10, Keyboard, Mouse	\$ 995.00
Monitor – Samsung 390 Series 24" Equipment Sub-Total:	\$ 160.00 \$6,350.00
Discount:	\$ <500.00>
Equipment Sub-Total:	\$ 5,850.00
CA Sales Tax 8.50% Sub-Total:	\$ 497.25 \$ 6,347.25
Onsite Install/Training Freight One Year Service Contract	\$ 500.00 \$ 75.00 \$ 935.00
Total Investment:	\$ 7,857.25

<sup>\*</sup> Pricing with discounting above is based on complete configuration and valid for 30 days.

AUTHORIZED KODAK & ST IMAGING Products
Formerly Bell & Howell

#### ST ViewScan Maintenance Agreement

Includes Advanced Unit Replacement During Repair. If part is defective, Total Imaging Solutions will overnight a replacement part – with pre-paid label to return the defective part. While under service contract, Total Imaging Solutions is responsible for all repairs and/or shipping of similar ST ViewScan components to end customer site while repair is performed. If necessary, a loaner would be provided. All ST ViewScan Software upgrades are included in Service Contract. Additional training is included in service contract.

ST ViewScan 4 with 9 mp System with Motorized Film/Fiche \$935.00/Year

#### <u>Installation and Training Process</u>

#### Starting Out Right Is Key!

Total Imaging Solutions provides a complete installation and training onsite with the customer. Initial setup and testing is done with your IT person. At that time, we train IT on the software and hardware so that IT understands all components of the ST ViewScan software and functions. Initial set up and testing takes two hours. A Pre-Installation Check List is sent out to IT to confirm that the PC Specifications are met before the installation takes place. See the minimum PC Specifications required – below. Staff training is scheduled the same day. The first hour is showing all of the software features and functions. The second hour is spent with hands-on with the Staff and having them go through the features. More time is allotted if needed. Follow-up is provided periodically.

AUTHORIZED KODAK & ST IMAGING Products
Formerly Bell & Howell

# ST ViewScan 4 Minimum/ Recommended PC Specifications Requirements

Item	Specifications
USB 3.0 Ports	Minimum of (2) USB 3.0 Ports required for connection
	to camera (must have Driver update of 2014 or newer)
	PC must come with integrated USB 3.0 ports that have
	either an "SS" next to them or are blue.
Memory	8GB RAM
***	16GB RAM recommended
Processor Speed	I5 Processor, i7
	2.4 Gig HZ or faster
Video Card	1+ GB Discrete Video Card or Greater, NVIDIA
	GeForce GTX 700 series recommended, certified to
	work. Motherboard shared graphics processors,
	relying on Intel HD, or 93/95 Chipset, as examples will
	not work properly.
Operating System	Original Installed Operating System on PC must be
	Windows 7 or 8 or 10
	64 Bit Preferred
¥	.net framework 4.0 is required
-	Latest service pack is recommended
USB 2.0 Ports	Minimum of (2) USB 2.0 Ports, 4 recommended.
Monitor	22" or 24" with latest video driver. 1280 x1024 screen
	resolution. (The larger the monitor, the better the
	image, also rotating monitor can be helpful)
PC	I5 or I7 preferred, minimum Intel Core Duo